

WADING POOL® LAVATORY K-2314

ADA


Features

- Fireclay
- Without overflow
- Countertop or wall-mount installation
- Available without faucet holes, single hole (-1), 4" (10.2 cm) centers (-4), or 8" (20.3 cm) centers (-8)
- Complements the Purist Suite
- 24" (61 cm) x 23-1/2" (59.7 cm)

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ADA
- ASME A112.19.2/CSA B45.1
- ICC/ANSI A117.1



Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- NA: None applicable

Specified Model

Model	Description	Colors/Finishes	
K-2314	Wading Pool lavatory - without faucet holes (shown)	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-2314-1	Wading Pool lavatory - single-hole	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-2314-4	Wading Pool lavatory - 4" (10.2 cm) centers	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-2314-8	Wading Pool lavatory - 8" (20.3 cm) centers	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Recommended Accessories

K-9583	Bracket kit - includes right and left-facing brackets for wall-mount installation	<input type="checkbox"/> NA
K-7605-P	Lavatory supplies	<input type="checkbox"/> CP <input type="checkbox"/> PB <input type="checkbox"/> Other_____
K-9018	P-Trap	<input type="checkbox"/> CP <input type="checkbox"/> PB <input type="checkbox"/> Other_____
K-7715	Grid drain	<input type="checkbox"/> CP <input type="checkbox"/> PB <input type="checkbox"/> Other_____

Refer to the Price Book for countertop and hand basin options.

Product Specification

The fireclay lavatory shall be 24" (61 cm) in length and 23-1/2" (59.7 cm) in width. Product shall be available with no faucet holes, single-hole, 4" (10.2 cm) centers, or 8" (20.3 cm) centers. Product shall be suitable for countertop or wall-mount installation. Product shall be without overflow. Product shall complement the Purist Suite. Product shall be Kohler Model K-2314-_____-_____.

PURIST®

Technical Information


Fixture*:		
Basin area	22" (55.9 cm) x 17-1/2" (44.5 cm)	
Water depth	1-3/4" (4.4 cm)	
Drain hole	1-3/4" (4.4 cm) D.	
Hole diameter:		
	Spout	Faucet
K-2314-1	1-3/8" (3.5 cm) D.	
K-2314-4	1-3/16" (3 cm) D.	1-3/16" (3 cm) D.
K-2314-8	1-3/16" (3 cm) D.	1-7/16" (3.7 cm) D.
* Approximate measurements for comparison only.		
Included component:		
Cut-out template	1014137-7	

Installation Notes

Install this product according to the installation guide.

Product does not have an overflow.

NOTICE: Countertop manufacturer or cutter **must** use the cut-out template provided with the product, or a current cut-out template provided by Kohler Co. (call 1-800-4-KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect template is used.



Product Diagram