


### Features

- Acrylic
- Pump with air switch and grounding-type plug-in cord
- 6 individually adjustable multi-directional hydro-massage jets
- Left or right drain
- In-line heater
- Optional K-1283 removable apron
- Optional K-1717 timer kit
- Optional K-1491 removable bath pillow
- Optional K-9696 whirlpool trim kit in various finishes
- 72" (182.9 cm) x 36" (91.4 cm) x 20" (50.8 cm)

### BATH WHIRLPOOL WITH CUSTOM PUMP K-1257-CB



### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- ASME A112.19.7M
- UL 1795

### Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

### Accessories

- 0: White
- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- NA: None applicable
- Other: Refer to Price Book for additional colors/finishes

### Specified Model

Model	Description	Colors/Finishes	
K-1257-CB	Bath whirlpool with custom pump – drop-in rim style	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Recommended Accessories			
K-7166-AF	Adjustable pop-up drain – above or through-the-floor installation	<input type="checkbox"/> CP	<input type="checkbox"/> PB <input type="checkbox"/> Other_____

Optional Accessories					
K-1283	Removable apron			<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1491	Pillow			<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1717	20-minute ProFlex timer kit	<input type="checkbox"/> NA			
K-9696	Jet trim kit – metal finishes		<input type="checkbox"/> CP <input type="checkbox"/> PB		<input type="checkbox"/> Other_____

### Product Specification

The acrylic bath whirlpool shall be 72" (182.9 cm) in length, 36" (91.4 cm) in width, and 20" (50.8 cm) in height. Product shall have 6 individually adjustable multi-directional hydro-massage jets, a pump with air switch, and grounding-type plug-in cord. Product shall have an optional K-1283 removable apron, K-1491 removable bath pillow, K-1717 timer kit, and K-9696 trim kit in various finishes. Bath whirlpool shall be Kohler Model K-1257-CB-\_\_\_\_\_.

# MARIPOSA®

## Technical Information

Fixture*:			
Bathing well:			
Basin area, bottom	50" (127 cm) x 24" (61 cm)		
Basin area, top	65" (165.1 cm) x 27" (68.6 cm)		
Weight	110 lbs (49.9 kg)		
To overflow:			
Water depth	14" (35.6 cm)		
Capacity	72 gal (272.5 L)		
* Approximate measurements for comparison only.			
Drop-in cut-out			
		70" (177.8 cm) x 34" (86.4 cm)	
Pump:			
	V	Hz	A
1-speed	120	60	7.5

## Required Electrical Service


Dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI):	
Pump/control	120 V, 15 A, 60 Hz
Locate the outlet behind the whirlpool and within 24" (61 cm) of the pump.	

## Installation Notes

Install this product according to the installation guide.

Floor support under whirlpool must provide for a minimum of 41 lbs/square foot (200 kg/square meter) loading.

The apron must be installed before the finished floor and wall materials are installed.



## Product Diagram