


Features

- Acrylic
- Pump with air switch and grounding-type plug-in cord
- In-line heater
- Left or right drain
- Optional K-1283 removable apron
- Optional K-1491 removable bath pillow
- Optional K-1717 20-minute ProFlex® timer kit
- Drop-in installation [-H] or 3-side integral tile flange for alcove installation [-LH, -RH]
- 6 individually adjustable multi-directional hydro-message jets
- 72" (182.9 cm) x 36" (91.4 cm) x 20" (50.8 cm)

BATH WHIRLPOOL WITH IN-LINE HEATER

K-1257-H

ALSO K-1257-LH, K-1257-RH



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- ASME A112.19.7M
- UL 1795

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- NA: None applicable

Specified Model

Model	Description	Colors/Finishes	
K-1257-H	Bath whirlpool with in-line heater – drop-in rim style	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1257-LH	Bath whirlpool with in-line heater – 3-side integral flange, left drain	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1257-RH	Bath whirlpool with in-line heater – 3-side integral flange, right drain	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Recommended Accessories

K-7166-AF	Adjustable pop-up drain – above or through-the-floor installation	<input type="checkbox"/> CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other_____
-----------	---	-----------------------------	-----------------------------	-------------------------------------

Optional Accessories

K-1283	Removable apron	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1491	Pillow	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Product Specification

The acrylic bath whirlpool shall be 72" (182.9 cm) in length, 36" (91.4 cm) in width, and 20" (50.8 cm) in height. Product shall be for drop-in installation [-H] or 3-side integral tile flange for alcove installation [-LH, -RH]. Product shall have a left or right drain. Product shall have 6 individually adjustable multi-directional hydro-massage jets, a pump with air switch and grounding-type plug-in cord, and an in-line heater. Product shall have an optional K-1283 removable apron, K-1491 removable bath pillow, and K-1717 20-minute Proflex timer kit. Bath whirlpool shall be Kohler Model K-1257-____-____.

MARIPOSA®

Optional Accessories

K-1717	20-minute ProFlex timer kit				<input type="checkbox"/> NA
K-9696	Jet trim kit – metal finishes	<input type="checkbox"/> CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other_____	

Technical Information


Fixture*:	
Bathing well:	
Basin area, bottom	50" (127 cm) x 24" (61 cm)
Basin area, top	65" (165.1 cm) x 27" (68.6 cm)
Weight	115 lbs (52.2 kg)
To overflow:	
Water depth	14" (35.6 cm)
Capacity	72 gal (272.5 L)
* Approximate measurements for comparison only.	

Drop-in cut-out	70" (177.8 cm) x 34" (86.4 cm)
-----------------	--------------------------------

Pump:		V	Hz	A
1-speed		120	60	7.5
Heater:	kw	V	Hz	A
	1.5	120	60	12.5

Minimum access panel for pump/control	
20" (50.8 cm) W x 15" (38.1 cm) H	required

Pump/Control Access (If Apron Is Not Used):
20" (50.8 cm) W x 15" (38.1 cm) H



Required Electrical Services

Two dedicated circuits required, each protected with Class A Ground-Fault Circuit-Interrupter (GFCI):	
Pump/control	120 VAC, 15 A, 60 Hz
Heater	120 VAC, 15 A, 60 Hz
Locate the outlet behind the whirlpool and within 24" (61 cm) of the pump and heater.	

Installation Notes

Install this product according to the installation guide.


Floor support under whirlpool must provide for a minimum of 41 lbs/square foot (201 kg/square meter) loading.

The apron must be installed before the finished floor and wall materials are installed.


If installing a rim-mount faucet, make sure there is no interference with drain overflow and circulating system before drilling any holes. Consult local and national codes for minimum air gap requirements if installing a spout on the faucet deck.

No change in measurements if connected with drain illustrated. (K-11677 or K-11677M)

Recommended Faucet Area



Pump/Control Access
(If Apron Is Not Used):
20" (50.8 cm) W x 15"
(38.1 cm) H



Product Diagram