

STAINLESS STEEL SINK K-3369


Features

- 18-gauge stainless steel
- Self-rimming
- Double (equal) compartment
- 4-hole (-4), 3-hole (-3), or single-hole (-1)
- Includes SilentShield® sound-absorption technology
- Includes installation hardware
- 33" (83.8 cm) x 22" (55.9 cm) x 8" (20.3 cm)

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.3/CSA B45.4



Colors/Finishes

- NA: None applicable

Accessories:

- CP: Polished Chrome
- ST: Stainless Steel
- NA: None applicable

Specified Model

Model	Description	Colors/Finishes
K-3369-4	Kitchen sink – 4-hole faucet punching (shown)	<input type="checkbox"/> NA
K-3369-3	Kitchen sink – 3-hole faucet punching	<input type="checkbox"/> NA
K-3369-1	Kitchen sink – single-hole faucet punching	<input type="checkbox"/> NA

Optional Accessories

K-3194	Stainless steel bottom basin rack (for left basin only)	<input type="checkbox"/> ST
K-3196	Stainless steel bottom basin rack (for right basin only)	<input type="checkbox"/> ST
K-3370	Staccato hardwood cutting board	<input type="checkbox"/> NA
K-8813	Stainless steel sink strainer with tailpiece	<input type="checkbox"/> CP

Product Specification:

The 18 gauge stainless steel sink shall be 33" (83.8 cm) in length and 22" (55.9 cm) in width, and 8" (20.3 cm) in depth. Sink shall be self-rimming with double (equal) compartment. Sink shall be available with 4-hole, 3-hole, or single-hole faucet punching. Sink shall feature SilentShield sound deadening, which reduces disposal noise and vibration from dishes and running water. Sink shall include installation hardware. Sink shall be Kohler Model K-3369-__-____.

STACCATO™


Technical Information

Fixture*:	
Left and right compartments	
Basin areas	13-15/16" (35.4 cm) x 17-1/16" (43.3 cm)
Water depth	8" (20.3 cm)
Drain opening	3-5/8" (9.2 cm) D.
Faucet holes	1-7/16" (3.7 cm) D.
* Approximate measurements for comparison only.	
Included components:	
Installation hardware	1036072

Installation Notes

Install this product according to the installation guide.

Cutout is 32-1/2" (82.6 cm) x 21-1/2" (54.6 cm) with 1" (2.5 cm) radius corners.



Product Diagram