

Product Information

Applicable product	
4-hole utility sink, with two holes on each side	K-6607-4
3-hole utility sink, with holes in center deck	K-6607-3
Single-hole utility sink, with hole in center deck	K-6607-1

Fixture*:	
Bowl area	42-7/16" (1078 mm) x 18-1/2" (470 mm)
Water depth	10" (254 mm)
Faucet holes	Ø 1-3/8" (35 mm)
Drain holes	Ø 3-7/8" (98 mm)
* Approximate measurements for comparison only.	

Recommended accessories:	
Duostrainer® sink strainer	K-8801

Optional accessories:	
Wood grate	K-6026
Bottom bowl rack (left-side of drain)	K-6029L
Bottom bowl rack (right-side of drain)	K-6029R
Cutting board	K-6035
Legs (pair) for wall-mount installation of sink	K-6617

Installation Notes

Install this product according to the installation guide.

Countertop cut-out is 44" (1118 mm) by 20" (508 mm) with 1-15/16" (49 mm) radius corners.

Fixture conforms to ASME Standard A112.19.1/CSA B45.2. All dimensions are nominal.

