

Product Information

Applicable product with or without painted underside of sink:	
Single-hole sink, with holes on top of backsplash	K-6608-1, K-6608-1P
2-hole sink, with holes on front of backsplash	K-6608-2, K-6608-2P
3-hole sink, with holes on top of backsplash	K-6608-3, K-6608-3P

Fixture*:	
Bowl area	20-9/16" (522 mm) x 17-1/8" (435 mm)
Water depth	11" (279 mm)
Water capacity	16.5 gal (62.4 L)
Faucet holes	1-3/8" (35 mm)
Drain hole	3-7/8" (98 mm)
* Approximate measurements for comparison only.	

Recommended accessories:	
Duostrainer® sink strainer	K-8801
Optional accessories:	
Wood grate	K-6027
Bottom bowl rack	K-6034
Wood sink stand	K-6618

Installation Notes

Install this product according to the installation guide.

Countertop cut-out is 24-1/2" (622 mm) by 19-3/4" (502 mm) with 1/2" (13 mm) radius corners.

Fixture conforms to ASME Standard A112.19.1/CSA B45.2. All dimensions are nominal.

