


Features

- Heavy gauge aluminum framed construction
- For use with standard or steam shower applications
- Available with or without operating transom
- Right or left door swing
- CleanCoat™ glass coating
- 5/16" (0.8 cm) clear tempered glass
- 48" (121.9 cm) door - 1-1/2" (3.8 cm) of adjustability
- 36" (91.4 cm) door - 1" (2.5 cm) of adjustability
- 48" (121.9 cm) door fits K-9025 Kathryn shower receptor

STEAM PIVOT SHOWER DOORS K-702210

ALSO K-702212, K-702214, K-702216



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z97.1 (tempered glass)

Colors/Finishes

- SH: Bright Silver
- NX: Brushed Nickel
- FX: French Gold Anodized

Glass Options

- L: Clear

Specified Model



Model	Description	Glass Options	Colors/Finishes		
			<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> FX
K-702210	Kathryn 36" (91.4 cm) framed shower door	<input type="checkbox"/> L	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> FX
K-702212	Kathryn 48" (121.9 cm) framed shower door	<input type="checkbox"/> L	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> FX
K-702214	Kathryn 36" (91.4 cm) framed shower door with transom	<input type="checkbox"/> L	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> FX
K-702216	Kathryn 48" (121.9 cm) framed shower door with transom	<input type="checkbox"/> L	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> FX

Product Specification

The Kathryn framed shower door with CleanCoat™ glass coating shall have heavy gauge aluminum framed construction for use with standard or steam shower applications. The shower door shall have 5/16" (0.8 cm) clear tempered glass. The shower door shall be expandable from 45-1/2" (115.6 cm) to 47" (119.4 cm) wide for the 48" (121.9 cm) door and from 34" (86.4 cm) to 35" (88.9 cm) wide for the 36" (91.4 cm) door. 48" (121.9 cm) door shall fit K-9025 Kathryn shower receptor. The shower door shall swing left or right and be available with or without operating transom. The shower door shall be Kohler Model K-_____ - _____ - _____.

Installation Notes

Install this product according to the installation guide.



	A (Min - Max)	B (Min - Max)	C (Min - Max)	D (Min - Max)
K-702210	76" (193 cm) - 76-1/2" (194.3 cm) *		34" (86.4 cm) - 35" (88.9 cm)	
K-702212	76" (193 cm) - 76-1/2" (194.3 cm) *			45-1/2" (115.6 cm) - 47" (119.4 cm)
K-702214		89-1/8" (226.4 cm) - 89-5/8" (227.6 cm)	34" (86.4 cm) - 35" (88.9 cm)	
K-702216		89-1/8" (226.4 cm) - 89-5/8" (227.6 cm)		45-1/2" (115.6 cm) - 47" (119.4 cm)

* If unit is not a steam unit, door can be installed in any opening greater than 76" (193 cm).

Product Diagram