


Features

- KOHLER cast iron
- Acid-resistant enamel finish
- Undercounter
- Double (large/medium) compartment
- 4-hole (oversize)
- 23" (58.4 cm) undermount sink kit included
- 33" (83.8 cm) x 22" (55.9 cm)

ENAMELED CAST IRON UNDERCOUNTER SINK K-5814-4U



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.1/CSA B45.2

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- CP: Polished Chrome
- ST: Stainless Steel
- Other: Refer to Price Book for additional colors/finishes
- NA: None applicable

Specified Model

Model	Description	Colors/Finishes	
K-5814-4U	Enameled cast iron undercounter sink – 4-hole	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Recommended Accessories			
K-9000	Trap		<input type="checkbox"/> CP

Optional Accessories					
K-6056	Bottom basin rack (for left basin only)			<input type="checkbox"/> ST	
K-6057	Bottom basin rack (for right basin only)			<input type="checkbox"/> ST	
K-6622	Cutting board (for left basin only)		<input type="checkbox"/> NA		
K-6623	Colander		<input type="checkbox"/> NA		
K-8801	Duostrainer® sink strainer	<input type="checkbox"/> CP			<input type="checkbox"/> Other_____
K-5807	Undermount sink kit, 36" (91.4 cm)		<input type="checkbox"/> NA		

Product Specification

The undercounter sink shall be 33" (83.8 cm) in length and 22" (55.9 cm) in width. Sink shall be made of cast iron with acid resistant enamel finish. Sink shall have double (large/medium) compartment. Sink shall be 4-hole (oversized). Sink shall include 23" (58.4 cm) undermount sink kit. Sink shall be Kohler Model K-5814-4U-_____.

