


Features

- 18-gauge stainless steel
- Under-mount
- Single compartment
- Includes installation hardware
- 7-5/8" (194 mm) deep bowl
- 16-1/2" (419 mm) x 13-3/4" (349 mm)

UNDER-MOUNT KITCHEN SINK K-3184



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.3/CSA B45.4

Colors/Finishes

- NA: None applicable

Accessories

- NA: None applicable
- ST: Stainless Steel
- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Colors/Finishes
K-3184	Under-mount kitchen sink	<input type="checkbox"/> NA

Optional Accessories					
K-3128	Hardwood cutting board	<input type="checkbox"/> NA			
K-3134	Stainless steel bottom bowl rack		<input type="checkbox"/> ST		
K-8801	Duostrainer® sink strainer			<input type="checkbox"/> CP	<input type="checkbox"/> Other_____
K-8813	Stainless steel sink strainer with tailpiece			<input type="checkbox"/> CP	
K-8814	Stainless steel sink strainer, less tailpiece			<input type="checkbox"/> CP	

Product Specification

The under-mount kitchen sink shall be made of 18-gauge stainless steel. Sink shall be 16-1/2" (419 mm) in length and 13-3/4" (349 mm) in width with a 7-5/8" (194 mm) deep bowl. Sink shall be single compartment. Sink shall include installation hardware. Sink shall be Kohler Model K-3184-NA.

UNDERTONE®

Technical Information


Fixture*:	
Bowl area	16-1/2" (419 mm) x 13-3/4" (349 mm)
Water depth	7-5/8" (194 mm)
Drain hole	Ø 3-5/8" (92 mm)
*Approximate measurements for comparison only.	

Included components:	
Hardware kit	91915
Cut-out template	1016736-7

Installation Notes

Install this product according to the installation guide.

Allow a minimum of 2" (51 mm) minimum clearance around sink rim for clip attachment.



Product Diagram