


Features

- Cascading water over rim
- 4 kW 240 V heater
- Quiet 240 V pump with automatic shutdown
- With optional chromatherapy package
- Adjustable bath leveling system
- Left or right drain
- Effervescent bubbles with 11 ports
- Outer shell: 75" (190.5 cm) x 41" (104.1 cm) x 25" (63.5 cm)
- Interior rim: 63" (160 cm) x 31-1/2" (80 cm) x 23-1/2" (59.7 cm)
- Interior base: 45" (114.3 cm) x 25-1/2" (64.8 cm)

OVERFLOWING BATH K-1188-C1 ALSO K-1188-RE, K-1189-C1/-RE



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- ASME A112.19.7M
- UL 1795

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Colors/Finishes	
K-1188-C1	Overflowing bath – with chromatherapy lights, right drain (shown)	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1188-RE	Overflowing bath – right drain	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1189-C1	Overflowing bath – with chromatherapy lights, right drain	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1189-RE	Overflowing bath – left drain	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Required Accessory

K-7193	Adjustable pop-up drain - above or through-the-floor drain	<input type="checkbox"/> CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other_____
--------	--	-----------------------------	-----------------------------	-------------------------------------

Optional Accessory

K-1601	Footstop	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
--------	----------	----------------------------	-------------------------------------

Product Specification

The overflowing bath shall be made of fiberglass (FRP) with raised molded seat. Product shall have an outer shell dimension of 75" (190.5 cm) in length, 41" (104.1 cm) in width, and 25" (63.5 cm) in height. Product shall have an interior rim dimension of 63" (160 cm) in length, 31-1/2" (80 cm) in width, and 23-1/2" (59.7 cm) in depth. Product shall have an interior base dimension of 45" (114.3 cm) in length and 25-1/2" (64.8 cm) in width. Product shall feature cascading water over rim and effervescent bubbles with 11 effervescent ports. Product shall have a 4 kW (240 V) heater, quiet (240 V) pump with shutdown, and an adjustable bath leveling system. Overflowing bath shall be available with left or right drain and optional chromatherapy package. Overflowing bath shall be Kohler Model K-____-____-_____.

Technical Information

Fixture*:	
Bathing well:	
Basin area, bottom	45" (114.3 cm) x 25-1/2" (64.8 cm)
Basin area, top	63" (160 cm) x 31-1/2" (80 cm)
Weight	275 lbs (124.7 kg)
To overflow:	
Water depth	23-1/2" (59.7 cm)
Capacity	142 gal (537.5 L)
* Approximate measurements for comparison only.	

Drop-in cut-out	73-1/2" (186.7 cm) x 39-1/2" (100.3 cm)
-----------------	---

Pump:	V	Hz	A
	240	50/60	17
Heater:	4 kW	240	50/60
		50/60	17

Required Electrical Service (2 required)

Two dedicated circuits required, each protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD):

Pump/control	208-240 V, 20 A, 50/60 Hz
Heater	208-240 V, 20 A, 50/60 Hz

Installation Notes

Install this product according to the installation guide.

Two separate 240 V electrical services are required; one for the pump/control, and another for the heater.


Floor support under the overflowing bath must provide for a minimum of 65 lbs (317 kg).

Consult local and national codes for minimum air gap requirements when installing a spout on the bath deck.

Hot water supply should be 70% of capacity or greater. Installations will vary.

Unit must be filled through the bathing well.

No change in measurements with drain shown. (K-7193 or K-7193M)



Product Diagram