



### Features

- 3/4" (2 cm) adjustability per side
- Soft touch foam handle insert
- Corrosion proof
- Full length magnet provides secure door closure
- Tempered glass ensures maximum safety and durability
- Right or left door swing
- CleanCoat™ glass coating
- 72" (182.9 cm) height

### NEO-ANGLE SHOWER ENCLOSURES K-704516 ALSO K-704517



### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z97.1 (tempered glass)

### Colors/Finishes

- BH: Bright Brass
- SH: Bright Silver
- MX: Matte Nickel

### Glass Options

- B1: IntreX™
- L: Clear

### Specified Model

Model	Description	Glass Options		Frame Finishes/Colors		
K-704516	Shower enclosure - for use with K-1018 walls and K-9455 receptor	<input type="checkbox"/> B1	<input type="checkbox"/> L	<input type="checkbox"/> SH	<input type="checkbox"/> BH	<input type="checkbox"/> MX
K-704517	Shower enclosure - for use with K-9455 receptor	<input type="checkbox"/> B1	<input type="checkbox"/> L	<input type="checkbox"/> SH	<input type="checkbox"/> BH	<input type="checkbox"/> MX

#### Recommended Accessories

K-1018	Shower walls	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-9132	Shower drain with grid strainer	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-9455	Shower receptor	<input type="checkbox"/> CP	<input type="checkbox"/> Other_____

### Product Specification


The shower enclosure shall be 72" (182.9 cm) in height. The shower enclosure shall have right or left door swing with CleanCoat™ glass coating. The shower enclosure shall be corrosion proof. The shower enclosure shall have a soft touch foam handle insert, full length magnet to provide secure door closure, and tempered glass to ensure maximum safety and durability. The shower enclosure shall be Kohler Model K-\_\_\_\_\_-\_\_\_\_\_-\_\_\_\_\_.

# DEVONSHIRE®

## Installation Notes

Install this product according to the installation guide.

	A	B	C (Min-Max)	D (Min-Max)	E (Min-Max)	G (Walk Through)
K-704516	72" (182.9 cm)	27-3/4" (70.5 cm)	16-3/4" (42.5 cm) - 17-1/2" (44.5 cm)	35-3/8" (89.9 cm) - 36-1/8" (91.8 cm)	36-1/2" (92.7 cm) - 37-5/8" (95.6 cm)	21-3/4" (55.2 cm)
K-704517	72" (182.9 cm)	27-3/4" (70.5 cm)	17-15/16" (45.5 cm) - 18-11/16" (47.5 cm)	36-9/16" (92.8 cm) - 37-5/16" (94.8 cm)	38-7/32" (97.1 cm) - 39-5/16" (99.8 cm)	21-3/4" (55.2 cm)



## Product Diagram