


Features

- Smooth soft touch actuator
- Plumbing can be installed through wall or floor
- Vitreous china
- One-piece
- Less supply
- Comfort Height®
- Power Lite® operating system (see electrical service requirements)
- Includes Quiet-Close™ seat and cover
- 16-5/8" (422 mm) high bowl with seat
- 12" (305 mm) rough-in
- 1.6 gpf (6 lpf)



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- UL 1951

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- NA: None applicable

Specified Model

Model	Description	Colors/Finishes	
K-3492	Elongated bowl toilet	<input type="checkbox"/> 0 White	<input type="checkbox"/> Other_____

Product Specification:

Toilet shall have a smooth soft touch actuator. Plumbing may be installed through the wall or floor. Toilet shall be 1.6 gpf (6 lpf), with Power Lite™ flushing system. Toilet shall have a 12" (305 mm) rough-in. Toilet shall be made of vitreous china. Toilet shall be one piece and have an elongated bowl. Toilet shall include Quiet-Close™ seat and cover. Toilet shall be Comfort Height™. Bowl shall be 16-5/8" (422 mm) high with seat. Toilet shall be less supply. Toilet shall be Kohler Model K-3492-_____.

PURIST®

Technical Information


Fixture:				
Configuration	1-piece, compact elongated			
Water per flush	1.6 gallons (6 L)			
Passageway	2-1/8" (54 mm)			
Water area	12" (305 mm) x 9-1/2" (241 mm)			
Water depth from rim	4-7/8" (124 mm)			
Included Components:				
Seat	1022679			
Pump	HP	VAC	Hz	A
	1/5	120	60	8.5

Required Electrical Service

Dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI):	
Receptacle	120 VAC, 15 A, 60 Hz

Installation Notes

Install this product according to the installation guide.



Product Diagram