

**Features**


- MasterClean™ spray nozzles prohibit mineral build-up
- 72 individual spray nozzles
- Multi-function showerhead delivers wide, full coverage spray, aerated spray and massage spray
- 1/2" - 14 NPT connection
- Complements Bancroft® Suite
- 2.5 gal (9.5 L) per minute flow rate

**SHOWERHEAD**  
**K-10590**  
**ALSO K-10591**

**Codes/Standards Applicable**

Specified model meets or exceeds the following:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC



**Colors/Finishes**

- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

**Specified Model**


Model	Description	Colors/Finishes	
K-10590	Single-function showerhead	<input type="checkbox"/> CP	<input type="checkbox"/> Other ____
K-10591	Multi-function showerhead	<input type="checkbox"/> CP	<input type="checkbox"/> Other ____
Recommended Accessory			
K-7397	7-1/2" (13.7 cm) shower arm and flange	<input type="checkbox"/> CP	<input type="checkbox"/> Other ____

**Product Specification**

Showerhead shall include single or multi-function spray. Multi-function showerhead shall deliver wide, full coverage spray, soft aerated spray and therapeutic massage spray. Showerhead shall include MasterClean™ spray nozzles to prohibit mineral build-up. Showerhead shall include 72 individual spray nozzles. Showerhead shall have 1/2"-14 NPT connection. Showerhead shall be part of Bancroft Suite. Showerhead shall feature 2.5 gal (9.5 L) per minute flow rate. Showerhead shall be Kohler Model K-\_\_\_\_-\_\_\_\_.

## Installation Notes

Install this product according to the installation guide.



## Product Diagram