


Features

- Acrylic
- Oval shape
- Molded lumbar supports and armrests
- Optional K-1491 removable bath pillow
- Optional K-1601 removable footstop
- Textured bottom surface
- 60" (152.4 cm) x 42" (106.7 cm) x 21" (53.3 cm)



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- 0: White
- CP: Polished Chrome
- NA: None applicable
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Colors/Finishes		
K-1163	Bath	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____	
Recommended Accessories				
K-11677	Swiftflo™ adjustable trip lever drain	<input type="checkbox"/> CP	<input type="checkbox"/> Other_____	
Optional Accessories				
K-576	Undermount kit			<input type="checkbox"/> NA
K-1491	Pillow	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____	
K-1601	Footstop	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____	

Product Specification

The oval shaped bath shall be made of acrylic. Bath shall be 60" (152.4 cm) in length, 42" (106.7 cm) in width, and 21" (53.3 cm) in height. Bath shall have molded lumbar supports and armrests with textured bottom surface. Bath shall be Kohler Model K-1163-_____.

SUNWARD®

Technical Information


Fixture*:	
Bathing well:	
Basin area, bottom	43" (109.2 cm) x 24-5/8" (62.5 cm)
Basin area, top	53-1/2" (135.9 cm) x 32-1/8" (81.6 cm)
Weight	75 lbs (34 kg)
To overflow:	
Water depth	15" (38.1 cm)
Capacity	57 gal (215.9 L)
* Approximate measurements for comparison only.	
Included components:	
Cut-out template	1042556

Installation Notes

Install this product according to the installation guide.



Floor support under bath must provide for a minimum of 33 lbs/square foot (161 kg/square meter) loading.

No change in measurements if connected with drain illustrated.



No change in measurements if connected with drain illustrated. (K-11677 or K-11677M)

■ Recommended faucet area



Product Diagram