


### UNDERCOUNTER SINK K-3177 ALSO K-3177-L

#### Features

- 18-gauge stainless steel
- Undercounter
- Includes installation hardware
- Double (large/medium) compartment
- Squared bowl(s)
- 29-1/4" (74.3 cm) x 18-5/8" (47.3 cm)
- 9-1/2" (24.1 cm) deep left basin and 7-1/2" (19.1 cm) deep right basin (K-3177)
- 7-1/2" (19.1 cm) deep left basin and 9-1/2" (24.1 cm) deep right basin (K-3177-L)



#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.3/CSA B45.4

#### Colors/Finishes

- NA: None applicable

#### Accessories

- CP: Polished Chrome
- 0: White
- Other: Refer to Price Book for additional colors/finishes
- NA: None applicable

#### Specified Model

Model	Description	Colors/Finishes
K-3177	Undercounter sink with 9-1/2" (24.1 cm) deep left basin and 7-1/2" (19.1 cm) deep right basin	<input type="checkbox"/> NA
K-3177-L	Undercounter sink with 7-1/2" (19.1 cm) deep left basin and 9-1/2" (24.1 cm) deep right basin	<input type="checkbox"/> NA

Optional Accessories					
K-3190	Bottom basin rack	<input type="checkbox"/> 0			<input type="checkbox"/> Other_____
K-3277	Wire basket (for either basin)	<input type="checkbox"/> 0			<input type="checkbox"/> Other_____
K-3294	Hardwood cutting board (for either basin)		<input type="checkbox"/> NA		
K-8801	Duostrainer® sink strainer			<input type="checkbox"/> CP	<input type="checkbox"/> Other_____

#### Product Specification

The undercounter sink shall be 29-1/4" (74.3 cm) in length and 18-5/8" (47.3 cm) in width. Sink shall be made of 18 gauge stainless steel. Sink shall be double (large/medium) compartment with squared bowls. Kohler Model K-3177 sink shall have 9-1/2" (24.1 cm) deep left basin and 7-1/2" (19.1 cm) deep right basin. Kohler Model K-3177-L sink shall have 7-1/2" (19.1 cm) deep left basin and 9-1/2" (24.1 cm) deep right basin. Sink shall include installation hardware. Sink shall be Kohler Model K-3177-\_\_\_\_\_.

# UNDERTONE®



## Technical Information

<b>Dimensions shown for K-3177; sink dimensions are opposite for K-3177-L.</b>		
Fixture:*	Basin area	Water depth
Sink, left	14" (35.6 cm) x 19" (48.3 cm)	9-1/2" (24.1 cm)
Sink, right	14" (35.6 cm) x 16" (40.6 cm)	7-1/2" (19.1 cm)
Drain Holes	3-5/8" (9.2 cm) D.	
* Approximate measurements for comparison only.		

Included components:	
Hardware kit (4 required)	91915
Cut-out template (K-3177)	1040557-7
Cut-out template (K-3177-L)	1023161-7

## Installation Notes

Install this product according to the installation guide.



\* Allow clearance around sink rim for clip attachment.



## Product Diagram