


UNDERCOUNTER SINK **K-3166** ALSO K-3166-L

Features

- 18-gauge stainless steel
- Undercounter
- Includes installation hardware
- Rounded bowl(s)
- Triple compartment
- 39-3/8" (100 cm) x 17-7/8" (45.4 cm)
- 9-1/2" (24.1 cm) deep left basin, 7-1/2" (19.1 cm) deep right basin and 5-1/2" (14 cm) deep center basin (K-3166)
- 7-1/2" (19.1 cm) deep left basin, 9-1/2" (24.1 cm) deep right basin and 5-1/2" (14 cm) deep center basin (K-3166-L)



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.3/CSA B45.4

Colors/Finishes

- NA: None applicable

Accessories

- CP: Polished Chrome
- 0: White
- Other: Refer to Price Book for additional colors/finishes
- NA: None applicable

Specified Model

Model	Description	Colors/Finishes
K-3166	Undercounter sink with 9-1/2" (24.1 cm) deep left basin, 7-1/2" (19.1 cm) deep right basin and 5-1/2" (14 cm) deep center basin	<input type="checkbox"/> NA
K-3166-L	Undercounter sink with 7-1/2" (19.1 cm) deep left basin, 9-1/2" (24.1 cm) deep right basin and 5-1/2" (14 cm) deep center basin	<input type="checkbox"/> NA

Optional Accessories			
K-3280	Wire rinse basket (for either large basin)	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3291	Colander (for either large basin)	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3292	Hardwood cutting board and colander set (for small disposal basin)	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Product Specification

The undercounter sink shall be 39-3/8" (100 cm) in length and 17-7/8" (45.4 cm) in width. Sink shall be made of 18 gauge stainless steel. Sink shall be triple compartment with rounded bowls. Kohler Model K-3166 sink shall have 9-1/2" (24.1 cm) deep left basin, 7-1/2" (19.1 cm) deep right basin and 5-1/2" (14 cm) deep center basin. Kohler Model K-3166-L sink shall have 7-1/2" (19.1 cm) deep left basin, 9-1/2" (24.1 cm) deep right basin and 5-1/2" (14 cm) deep center basin. Sink shall include installation hardware. Sink shall be Kohler Model K-3166-_____.

UNDERTONE®

Optional Accessories (cont.)

K-3278	Hardwood cutting board (for either large basin)	<input type="checkbox"/> NA		
K-8801	Duostrainer® sink strainer		<input type="checkbox"/> CP	<input type="checkbox"/> Other_____

Technical Information

Dimensions shown for K-3166; sink dimensions are opposite for K-3166-L.

Fixture:*	Basin area	Water depth
Sink, left	14" (35.6 cm) x 18" (45.7 cm)	9-1/2" (24.1 cm)
Sink, right	14" (35.6 cm) x 18" (45.7 cm)	7-1/2" (19.1 cm)
Disposal, center	9" (22.9 cm) x 15" (38.1 cm)	5-1/2" (14 cm)
Drain Holes	3-5/8" (9.2 cm) D.	

* Approximate measurements for comparison only.


Included components:

Hardware kit (4 required)	91915
Cut-out template	1047579-7

Installation Notes

Install this product according to the installation guide.

K-3166 Shown



Product Diagram