

# KOHLER® Roughing-In

**K-6650, K-6652**  
**SUDBURY™**  
**SERVICE SINK**

## Product Information

Applicable product:	
Drilled back service sink	K-6650
Blank back service sink	K-6652

Fixture*:	
Basin area	19" (48.3 cm) x 16" (40.6 cm)
Water depth	13-1/8" (33.3 cm)
Drain hole	3" (7.6 cm) D.
Faucet holes (K-6650)	1-1/2" (3.8 cm) D.
* Approximate measurements for comparison only.	

Recommended accessories:	
P-Trap std. (for 2" iron pipe)	K-6672
P-Trap std. (for 3" iron pipe)	K-6673
Knoxford faucet for K-6652	K-8904
Kinlock faucet for K-6652	K-8907
Kinlock faucet for K-6652	K-8908

Optional accessories:	
Stainless steel rim guards for 9" (22.9 cm) sides	K-8932

Optional accessories:	
Stainless steel rim guards for 12" (30.5 cm) front	K-8934

Included component:	
Wall bracket	64512

## Installation Notes

Install this product according to the installation guide.

No change in sink measurements when used with K-6672 or K-6673 trap standard.

Fixture conforms to ASME Standard A112.19.2/CSA B45.1. All dimensions are nominal.

