

VESSEL™ LAVATORY K-19047


Features

- Fireclay
- With overflow
- Above-the-counter
- 16-1/8" (41 cm) x 16-1/8" (41 cm)

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1



Colors/Finishes

- 0: White
- 47: Almond
- 96: Biscuit

Specified Model

Model	Description	Colors/Finishes		
K-19047	Vessel lavatory with overflow	<input type="checkbox"/> 0	<input type="checkbox"/> 47	<input type="checkbox"/> 96

Product Specification

The vessel lavatory shall be 16-1/8" (41 cm) in length and 16-1/8" (41 cm) in width. Lavatory shall be made of fireclay and mounted above-counter. Lavatory shall have overflow. Lavatory shall be Kohler Model K-19047-_____.

ESCALE®


Technical Information

Fixture*:	
Basin area	16-1/8" (41 cm) x 16-1/8" (41 cm)
Water depth	3-1/2" (8.8 cm)
Drain hole	1-11/16" (4.3 cm) D.
*Approximate measurements for comparison only.	
Included component:	
Cut-out template	1052863-7

Installation Notes

Install this product according to the installation guide.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler (call 1-800-4-KOHLER). Kohler is not responsible for cutout errors when incorrect cut-out template is used.



Product Diagram