

Product Information

Applicable product:	
Elongated bowl toilet, left-hand trip lever	K-3531
Elongated bowl toilet, right-hand trip lever	K-3531-RA
Elongated bowl toilet with tank cover locks, left-hand trip lever	K-3531-T
Elongated bowl toilet with tank cover locks, right-hand trip lever	K-3531-TR

Fixture:	
Configuration	two-piece, elongated
Water per flush	1.0 gpf (4.0 lpf)
Passageway	2-1/4" (5.7 cm)
Water area	11-1/2" (29.2 cm) x 9-1/2" (24.1 cm)
Water depth from rim	5-5/8" (14.3 cm)
Seat post hole centers	5-1/2" (14 cm)
Maximum static pressure required	35 psi (241 kPa)
Maximum static pressure	80 psi (551.6 kPa)

Included components*:	
Bowl	K-4303
Tank	K-4484
Tank cover	1036375
Bolt cap accessory pack	52048
Tank accessory pack	73062
Trip lever, left-hand	K-9481-L
Trip lever, right-hand	K-9481-R
* Equipped with Sloan Flushmate® - Sloan Valve Company	

Installation Notes

Install this product according to the installation guide.

For back-to-back installations, the toilet shall be connected to the vertical stack using one of the three following fittings: double fixture fitting, double combination wye and 1/8 bends, or double wye and 1/8 bends.

Fixture conforms to ASME Standard A112.19.2/CSA B45.1. All dimensions are nominal.

