

### Product Information

Applicable product:	
Elongated bowl toilet, left-hand trip lever	K-3519
Elongated bowl toilet, right-hand trip lever	K-3519-RA
Elongated bowl toilet with tank cover locks, left-hand trip lever	K-3519-T
Elongated bowl toilet with tank cover locks, right-hand trip lever	K-3519-TR
ADA compliant when installed following installation notes. <b>ADA</b>	

Fixture:	
Elongated bowl toilet	two-piece, elongated
Water per flush	1.0 gpf (4.0 lpf)
Passageway	2-1/4" (5.7 cm)
Water area	11-1/2" (29.2 cm) x 9-1/2" (24.1 cm)
Water depth from rim	5-3/4" (14.6 cm)
Seat post hole centers	5-1/2" (14 cm)
Minimum static pressure required	35 psi (241 kPa)
Maximum static pressure	80 psi (551.6 kPa)

Included components:	
Bowl	K-4304
Tank	K-4484
Tank cover	1036375
Trip lever, left-hand	K-9481-L
Trip lever, right-hand	K-9481-R

### Installation Notes

Install this product according to the installation guide.

Will comply with the American Disabilities Act (ADA) when installed per the requirements of the Accessibility Guidelines, Section 604 Water Closets, of the Act. The Model Plumbing Codes require the installation of elongated open-front toilet seats in public bathrooms.

The Plumbing Codes require open-front elongated toilet seats on public use toilets.

For back-to-back installations, the toilet shall be connected to the vertical stack using one of the three following fittings: double fixture fitting, double combination wye and 1/8 bends, or double wye and 1/8 bends.

Fixture conforms to ASME Standard A112.19.2/CSA B45.1. All dimensions are nominal.

