


Features

- Acrylic
- Blower motor with 300 W heater, and electronic user control
- Blower motor is supplied with a grounding-type plug-in cord
- 120 BubbleMassage™ airjets
- Drop-in
- Low threshold height
- Slotted overflow for maximum bathing depth
- Integral lumbar support
- Armrests
- 72" (182.9 cm) x 36" (91.4 cm) x 19" (48.3 cm)

6' (1.8 m) BUBBLEMASSAGE™ BATH K-1124-G

ADA



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ADA
- ANSI Z124.1.2
- UL 1795
- IAPMO/UPC IGC 171

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- 0: White
- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Colors/Finishes	
K-1124-G	Drop-in rim style	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
Required Accessories			
K-7272	Drain – above or through-the-floor installation	<input type="checkbox"/> CP	<input type="checkbox"/> Other_____
Recommended Accessories			
K-1446	Remote blower installation kit		NA
Optional Accessories			
K-9529	Removable bath seat		<input type="checkbox"/> 0

Product Specification

The acrylic bath with airjets shall be 72" (182.9 cm) in length, 36" (91.4 cm) in width, and 19" (48.3 cm) in height. Bath shall have a blower motor with 300 W heater and an electronic user control. The blower motor shall have a grounding-type plug-in cord. Bath shall have 120 BubbleMassage airjets. Bath shall have slotted overflow for maximum bathing depth and low threshold height. Bath shall have an integral lumbar support and armrests. The bath with airjets shall be Kohler Model K-1124-G-_____.

ARCHER™

Technical Information

Fixture*:				
Bathing well				
Basin area, bottom	51-3/8" (130.5 cm) x 21" (53.3 cm)			
Basin area, top	64-1/2" (163.8 cm) x 30-1/2" (77.5 cm)			
Weight	100 lbs (45.4 kg)			
To overflow				
Water depth	15" (38.1 cm)			
Capacity	72 gal (273 L)			
* Approximate measurements for comparison only.				
Drop-in cutout dimensions:				
70-1/2" (179.1 cm) x 34-1/2" (87.6 cm)				
Blower motor:	Heater	V	Hz	A
	300 W	120	60	5

Required Electrical Service

Dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI):	
Blower motor:	120 V, 15 A, 60 Hz
Blower motor is supplied with a 24" (61 cm) grounding-type plug-in cord.	

Installation Notes

Install this product according to the installation guide.


NOTICE: It is not necessary that the blower motor and check valve be relocated. The option is provided for the case that a particular installation makes this effort practical. For this option, however, **the blower motor and the check valve must be relocated together.** Do not relocate one without the other.

NOTICE: If the blower motor and check valve are relocated: Two access panels are required. Provide one access panel at the blower motor/control location and the other access panel at the control box. **If the blower motor and check valve are not relocated:** One access panel is required at the blower motor/control location.

Floor support under this product must provide for a minimum of 41 lbs/square foot (197 kg/square meter) loading.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

This product is designed for a drop-in installation only. It is not suited for use in a three-wall alcove with an overhead shower.



Product Diagram