

Product Information

Applicable product:	
Elongated bowl toilet – center push button	K-3654
Fixture:	
Configuration	two-piece, elongated
Water per flush	1.6 gpf (6 lpf) or 0.8 gpf (3 lpf)
Passageway	2" (5.1 cm)
Water area	4-1/2" (11.4 cm) x 5-3/4" (14.6 cm)
Water depth from rim	8-1/2" (21.6 cm)
Seat post hole centers	5-1/2" (14 cm)
Included components:	
Bowl	K-4322
Tank	K-4419
Tank cover	1052066
Push buttons	1035417

Installation Notes

IMPORTANT! The rough-in must be 12" (30.5 cm) or more from the base of the wall or baseboard. The base of the toilet fits tightly against the wall or baseboard. The toilet will not fit correctly if there is less than 12" (30.5 cm) of clear space between the base of the wall or baseboard and the centerline of the outlet. Install or relocate the supply and outlet as necessary to conform to rough-in dimensions.

NOTE: If a baseboard causes the rough-in to be less than 12" (30.5 cm), it must be cut or removed to allow space for the toilet.

If this toilet is installed to new construction, install a new supply stop following the dimensions in the diagram.

In installations with the supply stop installed, the existing supply stop may need to be relocated if it is less than 8-1/2" (21.6 cm) from the centerline of the toilet. Dry fit the toilet to confirm if the supply stop needs to be relocated.

The supplied hose will extend roughly 6" (15.2 cm) from the toilet. If the supplied hose does not reach the supply stop, a longer supply hose may be used.

Fixture conforms to ASME Standard A112.19.2/CSA B45.1. All dimensions are nominal.

