

### Product Information

Applicable product:	
Elongated bowl toilet – left-hand trip lever (shown)	K-3652
Elongated bowl toilet – right-hand trip lever	K-3652-RA
Elongated bowl toilet – left-hand trip lever with tank cover locks	K-3652-T
Fixture:	
Configuration	two-piece, elongated
Water per flush	1.1 gal (4.2 L)
Passageway	2-1/4" (5.7 cm)
Water area	12" (30.5 cm) x 10" (25.4 cm)
Water depth from rim	7" (17.8 cm)
Seat post hole centers	5-1/2" (14 cm)
Minimum static pressure required	35 psi (241.3 kPa)
Maximum static pressure	80 psi (551.6 kPa)

Included components*:	
Bowl	K-4327
Tank	K-4484
Tank cover	1036375
Floor screws and bolt caps	52049
Bolt cap accessory pack	52048
Tank accessory pack	73062
Trip lever, left-hand	K-9481-L
Trip lever, right-hand	K-9481-R
*Equipped with Sloan FLUSHMATE® – Sloan® Valve Company.	

### Installation Notes

Install this product according to the installation guide.

For back-to-back installations, the toilet must be connected to the vertical stack using one of the three following fittings: double fixture fitting, double combination wye and 1/8 bends, or double wye and 1/8 bends.

Fixture conforms to ASME Standard A112.19.2/CSA B45.1. All dimensions are nominal.

