

**Features**

- Metal construction
- One-piece, self-contained ceramic disc valve allows both volume and temperature control
- 2" (51 mm) diameter valve with lever handles
- 1-1/2" (38 mm) to 13-1/4" (337 mm) spout reach
- For wall-mount installation
- Meets CalGreen requirements for kitchen faucets
- 1.8 gallons (6.8 L) per minute maximum flow rate at 60 psi (4.1 bar)


**WALL-MOUNT KITCHEN SINK FAUCET  
K-6228**

**ADA**

**Codes/Standards Applicable**

Specified model meets or exceeds the following:

- ADA
- ICC/ANSI A117.1
- ASME A112.18.1/CSA B125.1
- ASME A112.18.3
- NSF 61
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations



**Colors/Finishes**

- CP: Polished Chrome
- VS: Stainless Steel
- Other: Refer to Price Book for additional colors/finishes

**Accessories**

- NA: None applicable

**Specified Model**

Model	Description	Colors/Finishes		
K-6228-C11	Wall-mount kitchen sink faucet with silver tube	<input type="checkbox"/> CP	<input type="checkbox"/> VS	
K-6228-C12	Wall-mount kitchen sink faucet with black tube	<input type="checkbox"/> CP	<input type="checkbox"/> VS	
K-6228-C13	Wall-mount kitchen sink faucet with gold tube			<input type="checkbox"/> Other _____
K-6228-C15	Wall-mount kitchen sink faucet with bronze tube			<input type="checkbox"/> Other _____

Optional Accessories		
1107026	Shallow roughing-in valve body kit	<input type="checkbox"/> NA
1107027	Deep roughing-in valve body kit	<input type="checkbox"/> NA
1151265	Low flow kit – reduces maximum flow to 1.5 gpm (5.7 lpm) at 60 psi (4.1 bar)	<input type="checkbox"/> NA
1151266	High flow kit – increases maximum flow to 2.2 gpm (8.3 lpm) at 60 psi (4.1 bar)	<input type="checkbox"/> NA

**Product Specification**

The wall-mount kitchen sink faucet shall be made of metal construction. Product shall meet CalGreen requirements for kitchen faucets. Product shall have a maximum flow rate of 1.8 gallons (6.8 L) per minute at 60 psi (4.4 bar). Product shall feature a one-piece, self-contained ceramic disc valve, which allows both volume and temperature control. Product shall feature a 2" (51 mm) diameter valve with lever handles and a 1-1/2" (38 mm) to 13-1/4" (337 mm) spout reach. Product shall be for a wall-mount installation. Faucet shall be Kohler Model K-6228-\_\_\_\_-\_\_\_\_.

