

Product Information

Applicable product:	
Two-piece toilet	K-3588
Fixture*:	
Configuration	two-piece
Water per flush	1.6 gpf (6 lpf) or .8 gpf (3 lpf)
Water depth from rim	9-3/4" (24.8 cm)
Seat post hole centers	6-1/4" (15.9 cm)
Minimum static pressure required	20 psi (137 kPa)
Maximum static pressure	80 psi (551 kPa)
*Approximate measurements for comparison only.	
Included components:	
Toilet seat	E70004
Waste connector assembly	1070830
Installation kit	1052927
Installation template	1059382
Bowl	K-4308
Tank	K-4472

Installation Notes

A 4" D. waste outlet is required for this installation.

A 1" (2.5 cm) gap between the toilet and the wall is required.

A flange is not required for installation of this product. If this installation will be to new construction, do not install a flange on the waste outlet.

This toilet must be secured to the floor using the supplied floor anchors and bolts. If the subfloor is made of thin oriented strand board (OSB), we recommend that 1/2" (1.3 cm) plywood be attached to the subfloor at the floor anchor locations.

Install this product according to the installation guide.

Fixture conforms to ASME Standard A112.19.2/CSA B45.1. All dimensions are nominal.

