

**LAVATORY FAUCET  
K-116**

**ADA**


**Features**

- Brass construction
- Flexible connections for easy installation
- Brass valve bodies
- Quarter-turn washerless ceramic disc valves
- 2.0 gallons (7.6 L) per minute flow rate
- Pop-up drain with lift rod and tailpiece
- 5" (12.7 cm) High Country™ swing spout
- Available with six-prong or lever handles

**Codes/Standards Applicable**

Specified model meets or exceeds the following:

- ASME A112.18.1
- Energy Policy Act of 1992
- California Energy Commission
- IAPMO/UPC
- NSF 14
- ADA





**Colors/Finishes**

- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

**Accessories**

- NA: None applicable
- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

**Specified Model**

Model	Description			<b>ADA</b>		
K-116-3	Lavatory faucet with six-prong handles	<input type="checkbox"/> CP	<input type="checkbox"/> PB			
K-116-4	Lavatory faucet with lever handles			<input type="checkbox"/> CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other ____

**Product Specification**

Two-handle widespread lavatory faucet shall be of brass construction. Faucet shall feature brass valve bodies. Faucet shall feature quarter-turn washerless ceramic disc valves. Product shall include flexible connections for easy installation, 5" (12.7 cm) High Country swing spout, pop-up drain with lift rod and tailpiece, and six-prong or lever handles. Faucet shall be rated at 2.0 gallons (7.6 L) per minute flow rate. Faucet shall be Kohler Model K-\_\_\_\_\_-\_\_\_\_\_-\_\_\_\_\_.

