

LAVATORY BASE FAUCET K-7422-K




Features

- Brass construction
- Brass valve bodies
- Quarter-turn washerless ceramic disc valves
- Pop-up drain with lift rod and tailpiece
- Variety of handle style options
- For 4" (10.2 cm) centers
- Available with standard or vandal-resistant Water-Guard® aerator
- 1.5 gallons (5.7 L) per minute
- 5-1/4" (13.3 cm) gooseneck spout

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ADA
- ASME A112.18.1/CSA B125.1
- Energy Policy Act of 1992
- EPA WaterSense®
- ICC/ANSI A117.1
- NSF 61



Colors/Finishes

- CP: Polished Chrome

Specified Model

Model	Description	Colors/Finishes			
K-7422-K	Triton® lavatory faucet with standard aerator but without handles	<input type="checkbox"/> CP			
Required Accessories (Includes Two Handles)					
K-16010-2	Triton® standard handles	<input type="checkbox"/> CP			
K-16010-3	Triton cross handles		<input type="checkbox"/> CP		
K-16010-4	Triton lever handles			<input type="checkbox"/> CP	
K-16010-5	Triton wristblade lever handles				<input type="checkbox"/> CP

Product Specification

Two-handle centerset lavatory faucet shall be made of brass construction with brass valve bodies. Faucet shall feature quarter-turn washerless ceramic disc valves, assuring positive handle stop positioning. Faucet shall feature a flow rate of 1.5 gallons (5.7 L) per minute. Product shall include 4" (10.2 cm) centers, 5-1/4" (13.3 cm) gooseneck spout, standard or vandal-resistant Water-Guard® aerator, and pop-up drain with lift rod and tailpiece. Base faucet shall be Kohler Model K-7422-_____-CP with Kohler Model K-16010-_____-CP handles.

TRITON®

Optional Accessories		
1160595	Medium Spray 0.35 gpm (1.32 lpm) – Insert only	<input type="checkbox"/> NA
_____	Additional flow options are available (refer to the Price Book)	<input type="checkbox"/> NA

Installation Notes

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.

