


CORALAIS® DECORATOR SERIES

**ENTERTAINMENT SINK BASE
FAUCET
K-15840-K**

Features

- Metal construction
- Reversible quarter-turn washerless ceramic disc valves
- 4" (10.2 cm) spout reach
- Stationary gooseneck spout
- For 8" (20.3 cm) centers
- Lower flow aerator options are available (refer to the Kohler Price Book)
- 2.2 gpm (8.3 lpm) maximum flow rate



Codes/Standards Applicable


Specified model meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- NSF 61
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations

Colors/Finishes

- CP: Polished Chrome

Specified Model

Model	Description	Colors/Finishes
K-15840-K	Entertainment sink base faucet	<input type="checkbox"/> CP
Required Accessories		 ADA
K-15850-4M	Lever handles with polished chrome insert	<input type="checkbox"/> CP


Product Specification

The entertainment sink base faucet shall be of metal construction. Product shall have a 2.2 gpm (8.3 lpm) maximum flow rate with lower flow aerator options available (refer to the Kohler Price Book). Product shall feature reversible quarter-turn washerless ceramic disc valves and a 4" (10.6 cm) spout reach. Product shall feature a stationary gooseneck spout. Product shall be for 4" (10.6 cm) centers. Faucet shall be Kohler Model K-15840-K-CP and required handles shall be Kohler Model K-15850-4M-CP.

CORALAIS® DECORATOR SERIES

Installation Notes

Install this product according to the installation guide.



Product Diagram