

**KITCHEN SINK FAUCET
K-15175**


Features

- Metal construction
- One-piece, self-contained ceramic disc valve allows both volume and temperature control
- Temperature memory allows faucet to be turned on and off at any temperature setting
- High-temperature limit setting for added safety
- Ground joint connections
- Available with an 8-1/2" (21.6 cm) or 10" (25.4 cm) swing spout reach
- Lower flow aerator options are available (refer to the Kohler Price Book)
- 2.2 gpm (8.3 lpm) maximum flow rate

Codes/Standards Applicable

Specified model meets or exceeds the following at date of manufacture:





- ADA
- ASME A112.18.1/CSA B125.1
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- NSF 61
- All applicable US Federal and State material regulations



Colors/Finishes

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes


Specified Model

Model	Description	Lever Handle		Loop Handle	
					
K-15175-P	Kitchen sink faucet – with 8-1/2" (21.6 cm) spout reach	<input type="checkbox"/> CP			
K-15175-PT	Kitchen sink faucet – with 10" (25.4 cm) spout reach	<input type="checkbox"/> CP	<input type="checkbox"/> Other ____		
K-15175-TL	Kitchen sink faucet – with 10" (25.4 cm) spout reach			<input type="checkbox"/> CP	<input type="checkbox"/> Other ____

Product Specification


The single-control kitchen sink faucet shall be of metal construction. Product shall have a maximum flow rate of 2.2 gallons (8.3 L) per minute with lower flow aerator options available (refer to the Kohler Price Book). Product shall feature a one-piece, self-contained ceramic disc valve, which allows both volume and temperature control. Product shall feature temperature memory, allowing the faucet to be turned on and off at any temperature setting. Product shall include ground joint connections. Product shall be available with an ADA compliant loop or lever handle. Product shall be available with an 8-1/2" (21.6 cm) or 10" (25.4 cm) swing spout reach. Faucet shall be Kohler Model K-15175-____-____.

CORALAIS®

Optional Accessories			
K-15179-A	12" (30.5 cm) swing spout with aerator	<input type="checkbox"/> CP	<input type="checkbox"/> Other _____

Installation Notes

Install this product according to the installation guide.



	A	B	C
K-15175-P	8-1/2" (21.6 cm)	5" (12.7 cm)	6-1/8" (15.6 cm)
K-15175-PT, K-15175-TL	10" (25.4 cm)	5-3/4" (14.6 cm)	6-7/8" (17.5 cm)

Product Diagram