


**LAVATORY FAUCET
K-16102**

ADA

Features

- Brass construction
- Brass valve bodies
- Quarter-turn washerless ceramic disc valves
- For 8" (20.3 cm) or 16" (40.6 cm) centers
- 5-1/4" (13.3 cm) spout
- 2.0 gallons (7.6 L) per minute flow rate [max at 60 psi (4.14 bar)]
- Lower flow aerator options are available (refer to the Kohler Price Book)
- Flexible connections for easy installation
- Pop-up drain with tailpiece
- Complements Revival® Suite



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.18.1/CSA B125.1
- IAPMO/UPC
- NSF 61
- Energy Policy Act of 1992
- ADA
- CSA International



Colors/Finishes

- CP: Polished Chrome
- BN: Brushed Nickel
- Other: Refer to Price Book for additional colors/finishes

Accessories

- NA: None applicable

Specified Model

Model	Description						
K-16102-4	Lavatory faucet - scroll handles	<input type="checkbox"/> CP	<input type="checkbox"/> BN	<input type="checkbox"/> Other ____			
K-16102-4A	Lavatory faucet - traditional handles				<input type="checkbox"/> CP	<input type="checkbox"/> BN	<input type="checkbox"/> Other ____
Optional Accessories							
40003	Wrench for long-stemmed ceramic valve bodies	<input type="checkbox"/> NA					


Product Specification

Two-handle widespread lavatory faucet shall be of brass construction. Faucet shall feature brass valve bodies. Faucet shall feature quarter-turn washerless ceramic disc valves, assuring positive handle stop positioning. Product shall have a 5-1/4" (13.3 cm) spout, and a pop-up drain with tailpiece. Product shall have a flow rate of 2 gallons (7.5 L) per minute with lower flow aerator options available (refer to the Kohler Price Book). Faucet shall be available with 8" (20.3 cm) or 16" (40.6 cm) centers and scroll or traditional handles. Product shall complement the Revival Suite. Faucet shall be Kohler Model K-16102-____-____.

REVIVAL®

Installation Notes

Install this product according to the installation guide.



Product Diagram