


ELONGATED TOILET K-3438

Features

- Vitreous china
- 14" (35.6 cm) rough-in
- 1.6 gpf (6 lpf)
- 2" (5.1 cm) glazed trapway
- Combination toilet
- Ingenium® flushing system
- Includes polished chrome trip lever
- Less seat and supply
- Available with right-hand trip lever (-RA), bedpan lugs (-L), Insuliner® insulated tank lining (-U), and tank cover locks (-T)
- Available with tank cover locks (-T)
- 10-7/8" (27.6 cm) x 9-1/8" (23.2 cm) water area
- 31" (78.7 cm) x 19-5/8" (49.8 cm) x 28" (71.1 cm)



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2
- Energy Policy Act of 1992
- IAPMO/UPC
- CSA International
- CSA B45.0
- CSA B45.1

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories:

- CP: Polished Chrome
- PB: Vibrant® Polished Brass

Specified Model

Model	Description	Trip Lever	Colors/Finishes	
K-3438	Elongated bowl toilet	left-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3438-T	Elongated bowl toilet with tank cover locks	left-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3438-U	Elongated bowl toilet with Insuliner	left-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3438-UT	Elongated bowl toilet with Insuliner and tank cover locks	left-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3438-RA	Elongated bowl toilet	right-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3438-TR	Elongated bowl toilet with tank cover locks	right-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3438-UR	Elongated bowl toilet with Insuliner	right-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3438-RZ	Elongated bowl toilet with Insuliner and tank cover locks	right-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-4276-L & K-4621	Elongated bowl toilet with tank cover locks	left-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-4276-L & K-4621-RA	Elongated bowl toilet with tank cover locks	right-hand	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Product Specification

The elongated combination toilet shall be made of vitreous china. Toilet shall be 31" (78.7 cm) in length, 19-5/8" (49.8 cm) in width, and 28" (71.1 cm) in height with a 10-7/8" (27.6 cm) x 9-1/8" (23.2 cm) water area. Toilet shall be for 14" (35.6 cm) rough-in. Toilet shall feature a 2" (5.1 cm) glazed trapway and include a polished chrome trip lever. The toilet shall be 1.6 gpf (6 lpf) with Ingenium flushing system. Toilet shall be available with a right-hand trip lever (-RA), bed pan lugs (-L), Insuliner insulated tank lining (-U), and tank cover locks (-T). Toilet shall be less seat and supply. The toilet shall be Kohler Model K-____-____, or K-____-____-____,

WELLWORTH®

Recommended Accessories

K-4664	Brevia™ closed-front seat	<input type="checkbox"/> 0			<input type="checkbox"/> Other_____
K-7637	Angle supply with stop - 3/8" NPT		<input type="checkbox"/> CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other_____

Optional Accessories

K-9404-L	Trip lever, left-hand – non-CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other_____
K-9404-R	Trip lever, right-hand – non-CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other_____

Technical Information

Fixture:	
Configuration	two-piece, elongated
Water per flush	1.6 gal (6 L)
Passageway	2" (5.1 cm)
Water area	10-7/8" (27.6 cm) x 9-1/8" (23.2 cm)
Water depth from rim	6" (15.2 cm)
Seat post hole centers	5-1/2" (14 cm)

Included components:

Bowl	K-4276
Tank	K-4621
Tank cover	84095
Trip lever	42528-CP
Bolt cap accessory pack	1013092

Installation Notes

Install this product according to the installation guide.

