

**KITCHEN SINK FAUCET  
K-377**

**ADA**


**Features**

- Brass construction
- Brass valve bodies
- Quarter-turn washerless ceramic disc valves
- For 8" (20.3 cm) centers
- Traditional lever handles
- Available with white handle inserts (-4P)
- 9-3/16" (23.3 cm) swing spout
- Lower flow aerator options are available (refer to the Kohler Price Book)
- 2.2 gpm (8.3 lpm) maximum flow rate

**Codes/Standards Applicable**

Specified model meets or exceeds the following:

- ADA
- ASME A112.18.1/CSA B125.1
- ICC/ANSI A117.1
- NSF 61
- Energy Policy Act of 1992



**Colors/Finishes**

- CP: Polished Chrome
- BN: Brushed Nickel

**Accessories**

- NA: None applicable

**Specified Model**


Model	Description	Colors/Finishes	
K-377-4M	Kitchen sink faucet – lever handles	<input type="checkbox"/> CP	<input type="checkbox"/> BN
K-377-4P	Kitchen sink faucet – lever handles with white handle inserts	<input type="checkbox"/> CP	<input type="checkbox"/> BN
Optional Accessories			
40003	Wrench for long-stemmed ceramic valve bodies	<input type="checkbox"/> NA	
1095353	Deep roughing-in kit for two-handle faucet and sidespray – fits 1-3/8" (3.5 cm) to 2-1/8" (5.4 cm) countertop thickness	<input type="checkbox"/> NA	

**Product Specification**

The two-handle kitchen sink faucet shall be of brass construction and brass valve bodies. Product shall have a maximum flow rate of 2.2 gallons (8.3 L) per minute with lower flow aerator options available (refer to the Kohler Price Book). Product shall feature quarter-turn washerless ceramic disc valves. Product 9-3/16" (23.3 cm) swing spout, traditional lever handles, and handspray. Product shall be available with white handle inserts (-4P). Product be for 8" (20.3 cm) centers. Faucet shall be Kohler Model K-377-\_\_\_\_-\_\_\_\_.

## Installation Notes

Install this product according to the installation guide.



**Product Diagram**