


**PROFESSIONAL KITCHEN SINK
FAUCET
K-6340**

ADA

Features

- Brass construction
- One-piece, self-contained ceramic disc valve allows both volume and temperature control
- Temperature memory allows faucet to be turned on and off at any temperature setting
- High-temperature limit setting for added safety
- 9" (22.9 cm) high-arch swing spout with integral sprayhead and retractable hose
- Integral vacuum breaker
- ADA compliant front lever handle
- Single-hole or three-hole installation options
- Lower flow aerator options are available (refer to the Kohler Price Book)
- 2.2 gpm (8.3 lpm) maximum flow rate



Codes/Standards Applicable

Specified model meets or exceeds the following at date of manufacture:

- ADA
- ASME A112.18.1/CSA B125.1
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- NSF 61
- All applicable US Federal and State material regulations

Colors/Finishes

- CP: Polished Chrome

Specified Model

Model	Description	Colors/Finishes
K-6340	Professional kitchen sink faucet – with matching color sprayhead	<input type="checkbox"/> CP
K-6340-BP	Professional kitchen sink faucet – with black sprayhead	<input type="checkbox"/> CP


Product Specification

The single-control professional kitchen sink faucet shall be of brass construction. Product shall have a maximum flow rate of 2.2 gallons (8.3 L) per minute with lower flow aerator options available (refer to the Kohler Price Book). Product shall feature a one-piece, self-contained ceramic disc valve, which allows both volume and temperature control. Product shall feature temperature memory, allowing the faucet to be turned on and off at any temperature setting. Product shall include a high-temperature limit setting for added safety. Product shall feature a 9" (22.9 cm) high-arch swing spout with integral sprayhead and retractable hose. Product shall feature an integral vacuum breaker and ADA compliant front lever handle. Product shall be for single-hole or three-hole installation options. Faucet shall be Kohler Model K-6340-CP or K-6340-BP-CP.

PROAVATAR®

Installation Notes

Install this product according to the installation guide.



Roughing-In Notes

	A	B	C	D	E
With escutcheon	11-1/8" (28.3 cm)	16-1/2" (41.9 cm)	14-3/8" (36.5 cm)	3-1/8" (7.9 cm)	2-5/8" (6.7 cm)
Without escutcheon	11-5/8" (29.5 cm)	16" (40.6 cm)	13-7/8" (35.2 cm)	2-5/8" (6.7 cm)	3-1/8" (7.9 cm)

Product Diagram