


### Features

- Acrylic
- Left or right drain
- 120 BubbleMassage™ airjets
- Blower motor with 300 W heater, electronic user control, and grounding-type plug-in cord
- Textured bottom surface
- UL listed
- Optional K-1491 removable bath pillow
- Optional K-1601 removable footstop
- Optional K-1283 removable apron
- Drop-in [-G] or 3-side integral flange [-GLF, -GRF]
- 72" (182.9 cm) x 36" (91.4 cm) x 20" (50.8 cm)

### 6' BUBBLEMASSAGE™ BATH K-1257-G ALSO K-1257-GLF, K-1257-GRF



### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- UL 1795
- ASTM E162
- ASTM E662
- UPC

### Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

### Accessories

- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- NA: None applicable

### Specified Model

Model	Description	Colors/Finishes	
K-1257-G	Bubblemassage bath – drop-in	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1257-GLF	Bubblemassage bath – 3-side integral flange, left drain	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1257-GRF	Bubblemassage bath – 3-side integral flange, right drain	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

#### Recommended Accessories

K-7161-AF	Adjustable pop-up drain	<input type="checkbox"/> CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other_____
-----------	-------------------------	-----------------------------	-----------------------------	-------------------------------------

#### Optional Accessories

K-1283	Removable apron	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____	
K-1446	Remote blower installation kit			<input type="checkbox"/> NA
K-1491	Removable pillow	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____	
K-1601	Removable footstop	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____	

### Product Specification

The acrylic Bubblemassage bath shall be 72" (182.9 cm) in length, 36" (91.4 cm) in width, and 20" (50.8 cm) in height. Bath shall be for drop-in [-G] or 3-side integral flange [-GLF, -GRF]. Bath shall have a blower motor with 300 W heater, electronic user control, and blower motor with grounding-type plug-in cord. Bath shall feature a textured bottom surface, 120 Bubblemassage airjets, and left or right drain. Bath shall have an optional K-1601 removable footstop, K-1283 removable apron, and K-1491 removable bath pillow available. Bath shall be UL listed. The Bubblemassage bath shall be Kohler Model K-1257-\_\_\_\_-\_\_\_\_.

