

FORTE® RITE-TEMP®

Features

- Metal construction
- Intended for use with Rite-Temp® or HiFlow Rite-Temp® valves
- Variety of handle style options
- Includes faceplate and handle
- Available with 5-1/4" (13.3 cm) diverter bath spout with NPT or slip-fit connection

PRESSURE-BALANCING BATH AND SHOWER VALVE TRIM

K-T10274
ALSO K-T10275

ADA

Codes/Standards Applicable

Specified model meets or exceeds the following:




- ASME A112.18.1
- CSA B125
- IAPMO/UPC
- ADA
- CSA International



Colors/Finishes

- CP: Polished Chrome
- NA: None applicable
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	 ADA	 ADA	 ADA
K-T10274-4	Bath/shower trim, sculpted lever handle, NPT spout	<input type="checkbox"/> CP <input type="checkbox"/> Other ____		
K-T10274-4A	Bath/shower trim, traditional lever handle, NPT spout		<input type="checkbox"/> CP <input type="checkbox"/> Other ____	
K-T10275-4	Bath/shower trim, sculpted lever handle, slip-fit spout	<input type="checkbox"/> CP <input type="checkbox"/> Other ____		
K-T10275-4A	Bath/shower trim, traditional lever handle, slip-fit spout		<input type="checkbox"/> CP <input type="checkbox"/> Other ____	
K-T10275-4G	Bath/shower trim, script lever handle, slip-fit spout			<input type="checkbox"/> CP <input type="checkbox"/> Other ____

Rite-Temp® valve must be ordered to complete trim.

Product Specification

Rite-Temp® pressure-balancing single-control bath and shower faucet trim shall be of metal construction. Bath and shower trim shall include showerhead with arm and flange, 5-1/4" (13.3 cm) diverter spout with NPT or slip-fit connection, and faceplate with handle. Faucet trim shall be K-T_____-_____-_____- and Rite-Temp® valve shall be K-304-_____-NA OR K-306-KS-NA HiFlow Rite-Temp® valve.

FORTE® RITE-TEMP®

Required Accessories

K-304-K	Rite-Temp® valve without stops, NPT connections OR	<input type="checkbox"/> NA
K-304-KS	Rite-Temp® valve with stops, NPT connections OR	<input type="checkbox"/> NA
K-306-KS	HiFlow Rite-Temp® valve with stops, NPT connections OR	<input type="checkbox"/> NA
K-304-KP	Rite-Temp® valve with PVC connections	<input type="checkbox"/> NA

Recommended Accessories

88526	HiFlow Rite-Temp® thin wall installation kit	<input type="checkbox"/> CP	<input type="checkbox"/> Other _____
-------	--	-----------------------------	---

Optional Accessories

1025388	Forte® deep roughing-in kit for Rite-Temp® valve (lever handles)	<input type="checkbox"/> NA
---------	--	-----------------------------

Installation Notes



WARNING: Risk of damage to the K-306-KS valve assembly. When using the K-306-KS valve in a fiberglass or acrylic installation, use the thin wall installation kit (88526).


Install this product according to the installation guide.

Install the Rite-Temp® valve according to the valve installation guide.

Avoid cross-flow conditions. Do not install shut-off device on either valve outlet.

Cap shower outlet if deck-mounted spout, diverter, or handshower is connected to the spout outlet.

Install straight pipe or tube drop of 7" (17.8 cm) to 18" (45.7 cm) with single elbow between valve and wall-mount spout.



Product Diagram