


MEMOIRS® CLASS FIVE®


Features

- Vitreous china
- Round-front
- 12" (30.5 cm) rough-in
- Class Five® flushing system
- 2-1/8" (5.4 cm) glazed trapway
- Combination toilet
- Less seat and supply
- 1.6 gpf (6 lpf) or 1.28 gpf (4.8 lpf)
- 16-1/2" (41.9 cm) high bowl
- 10-3/4" (27.3 cm) x 8-1/2" (21.6 cm) water area
- 28-3/8" (72.1 cm) x 17-13/16" (45.2 cm) x 31-1/2" (80 cm) (K-3509)
- 28-3/8" (72.1 cm) x 18-7/8" (47.9 cm) x 31-1/8" (79 cm) (K-3511)

COMFORT HEIGHT™ TOILET K-3509 ALSO K-3511



K-3509



K-3511

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- Energy Policy Act of 1992

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories:

- 0: White
- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Colors/Finishes	
K-3509	Round front bowl toilet with classic design	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-3511	Round front bowl toilet with stately design	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Recommended Accessories					
K-4639	Cachet™ Quiet-Close™ round, closed-front toilet seat with cover			<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-4662	Lustra™ round, closed-front toilet seat with cover			<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-7637	Angle supply with stop, annealed vertical tube and 3/8" NPT	<input type="checkbox"/> CP	<input type="checkbox"/> PB		<input type="checkbox"/> Other_____

Product Specification:

The round front combination toilet shall be 12" (30.5 cm) rough-in. Toilet shall be made of vitreous china. Toilet shall have 10-3/4" (27.3 cm) x 8-1/2" (21.6 cm) water area. Toilet shall be at comfort height with a 16-1/2" (41.9 cm) high bowl. Toilet shall be rated at 1.6 gallons (6 L) per flush or 1.28 gallons (4.8 L) per flush with Class Five™ flushing system. Toilet shall have 2-1/8" (5.4 cm) glazed trapway and EPDM flapper. Toilet shall be less seat and supply. Toilet shall be Kohler Model K-_____-_____.

