


**Features**

- Brass construction
- Brass valve bodies
- Quarter-turn washerless ceramic disc valves
- Flexible connections for easy installation
- For 8" (203 mm) or 16" (406 mm) centers
- Stationary spout
- Pop-up drain with lift rod and tailpiece
- 4-5/8" (117 mm) spout
- Available with six-prong or lever handles
- 1.5 gallons (5.7 liters) per minute maximum flow rate

**WIDESPREAD BATHROOM SINK FAUCET  
K-108**

**ADA** **CSA B651** **OBC**



**Codes/Standards Applicable**

Specified model meets or exceeds the following at date of manufacture:

- ADA
- ICC/ANSI A117.1
- CSA B651
- OBC
- ASME A112.18.1/CSA B125.1
- NSF 61
- All applicable US Federal and State material regulations
- EPA WaterSense®



**Colors/Finishes**

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

**Accessories**

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes
- NA: None applicable

**Specified Model**

Model	Description	Six-Prong Handles		Lever Handles	
			<input type="checkbox"/> CP <input type="checkbox"/> Other _____		<input type="checkbox"/> CP <input type="checkbox"/> Other _____
K-108-3	Widespread bathroom sink faucet – six-prong handles	<input type="checkbox"/> CP	<input type="checkbox"/> Other _____	<input type="checkbox"/> CP	<input type="checkbox"/> Other _____
K-108-4	Widespread bathroom sink faucet – lever handles			<input type="checkbox"/> CP	<input type="checkbox"/> Other _____

**Product Specification**

The two-handle widespread bathroom sink faucet shall be of brass construction with brass valve bodies. Product shall have a maximum flow rate of 1.5 gallons (5.7 liters) per minute. Product shall feature quarter-turn washerless ceramic disc valves, flexible connections for easy installation, a 4-5/8" (117 mm) spout reach, and a stationary spout. Product shall be for 8" (203 mm) or 16" (406 mm) centers. Product shall feature a pop-up drain with lift rod and tailpiece. Product shall be available with six-prong or lever handles. Faucet shall be Kohler Model K-108-\_\_\_\_-\_\_\_\_.

# ANTIQUETM


Optional Accessories				
K-9637	Small lever inserts, pair	<input type="checkbox"/> CP		
K-9657	Small lever inserts, pair			<input type="checkbox"/> Other _____
_____	Additional flow options are available (refer to the Kohler Price Book)		<input type="checkbox"/> NA	

## Installation Notes

Install this product according to the installation notes

Lower flow aerator options are available. Please refer to the Kohler Price Book.

**ADA, CSA B651, OBC** compliant when installed to the specific requirements of these regulations.



## Product Diagram