


**Features**

- Brass construction
- Brass valve bodies
- Quarter-turn washerless ceramic disc valves
- Flexible connections for easy installation
- For 8" (20.3 cm) or 16" (40.6 cm) centers
- Stationary spout
- Pop-up drain with lift rod and tailpiece
- 4-5/8" (11.7 cm) spout
- Available with six-prong or ADA compliant lever handles
- 1.5 gallons (5.7 liters) per minute maximum flow rate

**WIDESPREAD LAVATORY FAUCET  
K-108**

**ADA**



**Codes/Standards Applicable**

Specified model meets or exceeds the following at date of manufacture:

- ADA
- ASME A112.18.1/CSA B125.1
- ICC/ANSI A117.1
- NSF 61
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations




**Colors/Finishes**

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

**Accessories**

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes
- NA: None applicable

**Specified Model**

| Model   | Description  | Six-Prong Handles   |   | Lever Handles  |                                      |
|---------|--|---|---|--|--------------------------------------|
|         |  |  |  |  <b>ADA</b> |                                      |
| K-108-3 | Widespread lavatory faucet – six-prong handles           | <input type="checkbox"/> CP   | <input type="checkbox"/> Other _____  |  |                                      |
| K-108-4 | Widespread lavatory faucet – ADA compliant lever handles |   |   | <input type="checkbox"/> CP  | <input type="checkbox"/> Other _____ |

**Product Specification**


The two-handle widespread lavatory faucet shall be of brass construction with brass valve bodies. Product shall have a maximum flow rate of 1.5 gallons (5.7 liters) per minute. Product shall feature quarter-turn washerless ceramic disc valves, flexible connections for easy installation, a 4-5/8" (11.7 cm) spout reach, and a stationary spout. Product shall be for 8" (20.3 cm) or 16" (40.6 cm) centers. Product shall feature a pop-up drain with lift rod and tailpiece. Product shall be available with six-prong or ADA compliant lever handles. Faucet shall be Kohler Model K-108-\_\_\_\_-\_\_\_\_.

# ANTIQUETM

| Optional Accessories |  |                             |                             |                                      |
|----------------------|--|-----------------------------|-----------------------------|--------------------------------------|
| K-9637               | Small lever inserts, pair  | <input type="checkbox"/> CP |                             |                                      |
| K-9657               | Small lever inserts, pair  |                             |                             | <input type="checkbox"/> Other _____ |
| 40003                | Wrench for long-stemmed ceramic valve bodies                           |                             | <input type="checkbox"/> NA |                                      |
| _____                | Additional flow options are available (refer to the Kohler Price Book) |                             | <input type="checkbox"/> NA |                                      |

## Installation Notes

Install this product according to the installation notes



## Product Diagram