

Features


- Metal construction
- Brass valve body
- Quarter-turn washerless ceramic disc valves
- 9-3/8" (23.8 cm) swing spout reach
- Flexible connections for easy installation
- Available with or without matching finish sidespray
- Lower flow aerator options are available (refer to the Kohler Price Book)
- 2.2 gpm (8.3 lpm) maximum flow rate

HIGH SPOUT KITCHEN SINK FAUCET

K-12230

ALSO K-12231

ADA **CSA B651** **OBC**



Codes/Standards Applicable

Specified model meets or exceeds the following at date of manufacture:

- ADA
- ICC/ANSI A117.1
- CSA B651
- OBC
- ASME A112.18.1/CSA B125.1
- NSF 61
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations

Colors/Finishes

- CP: Polished Chrome
- BN: Brushed Nickel
- Other: Refer to Price Book for additional colors/finishes

Accessories

- NA: None applicable

Specified Model

Model	Description	Colors/Finishes		
K-12230	High spout kitchen sink faucet – without sidespray	<input type="checkbox"/> CP	<input type="checkbox"/> BN	<input type="checkbox"/> Other _____
K-12231	High spout kitchen sink faucet – with sidespray (shown)	<input type="checkbox"/> CP	<input type="checkbox"/> BN	<input type="checkbox"/> Other _____
Optional Accessories				
1030920	Sidespray deep roughing-in kit	<input type="checkbox"/> NA		

Product Specification


The single-control high spout kitchen sink faucet shall be of metal construction with a brass valve body. Product shall have a maximum flow rate of 2.2 gallons (8.3 L) per minute with lower flow aerator options available (refer to the Kohler Price Book). Product shall feature quarter-turn washerless ceramic disc valves. Product shall feature a 9-3/8" (23.8 cm) swing spout reach and flexible connections for easy installation. Product shall be available with or without a matching finish sidespray. Faucet shall be Kohler Model K-12230-____ **OR** K-12231-____.

FAIRFAX®

Installation Notes

Install this faucet following the installation instructions provided.

ADA, CSA B651, OBC compliant when installed to the specific requirements of these regulations.



Product Diagram